



ADVANTAGES

- Microfine glass media formed into plats separated by tapered corrugated aluminum separators
- One-piece seamless gasket for leak-free performance
- Efficiencies of 99.97% and 99.99% at 0.3 microns

Application	Built-up filter banks, rooftops, and air handlers in medical facilities, pharmaceuticals, and clean process manufacturing.
Frame	Wood
Gasket	Seamless PU foamed gasket
Media	Glass fiber
Separator	Aluminium
Sealant	Polyurethane
Max Temperature (°C)	80° C, 175° F
Comment	99.97% at 0.3µ to 99.99% at 0.3µ. Tested in accordance with IEST Recommended Practice for Testing HEPA Filters. See Literature 1803H for more details.