GIGAPLEAT NXDP (DH)







ADVANTAGES

- Individually VOC outgassing tested
- High media cleanliness
- Predicted removal efficiency and lifetime by Camfil's proprietary software
- Typical target gases: VOCs, acids, bases, dopants, refractories, ozone
- Multiple media types can be combined into the same filter
- Low pressure drop
- Low outgassing components

Application	Clean room recirculation air, clean room make up air			
Frame	Stainless steel;Galvanised steel			
Gasket	Polyurethane;EPDM			
Media	Activated Carbon;Impregnated Activated Carbon			
Sealant	Polyurethane			
Max Temperature (°C)	40°C			
Relative Humidity max	30% - 70%			
Particle cleanliness	ISO Class 6			
Comment	Gasket Position: 01 - downstream, 10 - upstream Outgassing: Individually outgassing tested for VOC emissions			

Туре	Target contaminant	Dimensions WxHxD (mm)	Airflow/pressure drop (m ³ /h/Pa)	Weight (kg)
NXDP B	Bases	592x592x292	3300/55	15
NXDP B	Bases	287x592x292	1600/55	10
NXDP A	Acids	592x592x292	3300/55	15
NXDP A	Acids	287x592x292	1600/55	10
NXDP V	Organics	592x592x292	3300/55	15
NXDP V	Organics	287x592x292	1600/55	10
NXDP ABV	Bases, Acids, Organics	592x592x292	3300/190	20
NXDP ABV	Bases, Acids, Organics	287x592x292	1600/190	12

Other target gas combinations are available on request.