GIGAPLEAT NXDP (PH)









ADVANTAGES

- Individually VOC outgassing tested
- High media cleanliness
- Predicted removal efficiency and lifetime by Camfil's proprietary software
- Typical target gases: VOCs, acids, bases, dopants, refractories, ozone
- Multiple media types can be combined into the same filter
- Low pressure drop
- Low outgassing components

Application	Clean room recirculation air, clean room make up air		
Frame	Stainless steel;Galvanised steel		
Gasket	Polyurethane;EPDM		
Sealant	Polyurethane		
Max Temperature (°C)	40		
Relative Humidity max	30% - 70%		
Particle cleanliness	ISO Class 6		
Comment	Gasket Position: 01 - downstream, 10 - upstream Frame : PH = Single Header Outgassing: Individually outgassing tested for VOC emissions		

Туре	Target contaminant	Dimensions WxHxD (mm)	Airflow/pressure drop (m³/h/Pa)	Weight (kg)
NXDP ABV	Bases, Acids, Organics	592x592x292	3300/190	20
NXDP V	Organics	592x592x292	3300/55	15
NXDP A	Acids	592x592x292	3300/55	15
NXDP B	Bases	592x592x292	3300/55	15
NXDP ABV	Bases, Acids, Organics	287x592x292	1600/190	12
NXDP V	Organics	287x592x292	1600/55	10
NXDP A	Acids	287x592x292	1600/55	10
NXDP B	Bases	287x592x292	1600/55	10

Other target gas combinations are available on request.