ACTICARB NUCLEAR





ADVANTAGES

- Proven product, the factory controlled characteristics of which are maintained after handling and transportation
- Parameters integrated into internal software for customer simulation
- High efficiency filter for safety and protection uses Individual test of the leak rate
- Individual certificate

| ApplicationNuclear industry; electricity production or researchFrameStainless steel;Steel, paintedGasket½ round 15 mm moulded neoprene foamMedia: 50 mm (2 inch) bed depth of chromium-free impregnated activated carbon; vibrated and tamped to meet leakage requirements Gas to trap: ICH2 Impregnate: KI and TEDA Particle size: 8 x 16 US Mesh per ASTM E11-87 (% mass > 8 mesh (2.36mm): max 5; % mass < 16 mesh (1.18mm): max 2.5) Relative Humidity: < 40% Temperature: 80°C maximum continues Adsorbent volume (liters): full size 65 liters +/- 35 kg - half size 32,5 liters +/- 17 kg Controls: Individual test run for leakages (< 2,5 x 10-4) and pressure drop & Initial decontamination for ICH3 by IRSN | | | | | | |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|--|--|--|
| Gasket ½ round 15 mm moulded neoprene foam Media: 50 mm (2 inch) bed depth of chromium-free impregnated activated carbon; vibrated and tamped to meet leakage requirements Gas to trap: ICH2 Impregnate: KI and TEDA Particle size: 8 x 16 US Mesh per ASTM E11-87 (% mass > 8 mesh (2.36mm): max 5; % mass < 16 mesh (1.18mm): max 2.5) Relative Humidity: < 40% Temperature: 80°C maximum continues Adsorbent volume (liters): full size 65 liters +/- 35 kg - half size 32,5 liters +/- 17 kg Controls: Individual test run for leakages (< 2,5 x 10-4) and pressure drop & | Application | Nuclear industry; electricity production or research | | | | |
| Media: 50 mm (2 inch) bed depth of chromium-free impregnated activated carbon; vibrated and tamped to meet leakage requirements Gas to trap: ICH2 Impregnate: KI and TEDA Particle size: 8 x 16 US Mesh per ASTM E11-87 (% mass > 8 mesh (2.36mm): max 5; % mass < 16 mesh (1.18mm): max 2.5) Relative Humidity: < 40% Temperature: 80°C maximum continues Adsorbent volume (liters): full size 65 liters +/- 35 kg - half size 32,5 liters +/- 17 kg Controls: Individual test run for leakages (< 2,5 x 10-4) and pressure drop & | Frame | Stainless steel;Steel, painted | | | | |
| activated carbon; vibrated and tamped to meet leakage requirements Gas to trap: ICH2 Impregnate: KI and TEDA Particle size: 8 x 16 US Mesh per ASTM E11-87 (% mass > 8 mesh (2.36mm): may 5; % mass < 16 mesh (1.18mm): max 2.5) Relative Humidity: < 40% Temperature: 80°C maximum continues Adsorbent volume (liters): full size 65 liters +/- 35 kg - half size 32,5 liters +/- 17 kg Controls: Individual test run for leakages (< 2,5 x 10-4) and pressure drop & | Gasket | 1⁄2 round 15 mm moulded neoprene foam | | | | |
| | Comment | activated carbon; vibrated and tamped to meet leakage requirements Gas to trap: ICH2 Impregnate: KI and TEDA Particle size: 8 x 16 US Mesh per ASTM E11-87 (% mass > 8 mesh (2.36mm): max 5; % mass < 16 mesh (1.18mm): max 2.5) Relative Humidity: < 40% Temperature: 80°C maximum continues Adsorbent volume (liters): full size 65 liters +/- 35 kg - half size 32,5 liters +/- 17 kg Controls: Individual test run for leakages (< 2,5 x 10-4) and pressure drop & | | | | |

| ActiCarb Nuclear ICH3 610x610x292 1200/300 78 ≤ 90 ActiCarb Nuclear ICH3 305x610x292 600/300 43 ≤ 90 ActiCarb Nuclear ICH3 305x610x292 600/300 43 ≤ 90 ActiCarb Nuclear ICH3 305x610x292 600/300 43 ≤ 90 ActiCarb Nuclear ICH3 610x610x292 1200/300 78 ≤ 90 | Туре | Target contaminant | Dimensions WxHxD (mm) | Airflow/pressure drop (m ³ /h/Pa) | Weight (kg) | Optimum RH (%) |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------|--------------------|-----------------------|----------------------------------------------|-------------|----------------|
| ActiCarb Nuclear ICH3 305x610x292 600/300 43 ≤ 90 | ActiCarb Nuclear | ICH3 | 610x610x292 | 1200/300 | 78 | ≤90 |
| | ActiCarb Nuclear | ICH3 | 305x610x292 | 600/300 | 43 | ≤90 |
| ActiCarb Nuclear ICH3 610x610x292 1200/300 78 ≤90 | ActiCarb Nuclear | ICH3 | 305x610x292 | 600/300 | 43 | ≤90 |
| | ActiCarb Nuclear | ICH3 | 610x610x292 | 1200/300 | 78 | ≤90 |