ACTICARB







ADVANTAGES

- Compatible with BIBO (Bag In Bag Out) housings
- Molecular filter for dangerous gases
- High filter efficiency
- Individual test of the leak rate
- Individual certificate

Application	Acticarb- ABEK: Defense, Civil and military protectionMERCURY: Research laboratories and production units for lamps and batteries ACID: Nuclear or other industries where hydrogen fluoride needs to be captured BASIC: Animal or research laboratories to capture ammonia VOC: When BIBO (Bag in Bag Out) is required to proceed to the VOC filter change NUCLEAR: Nuclear industry, electricity production or research MEDICAL: Hospitals with particle accelerator (cyclotron)
Frame	Stainless steel;Galvanised steel
Gasket	½ round 15 mm moulded neoprene foam
Comment	Media: 50 mm (2 inch) bed depth of Campure 8, high quality media; vibrated and tamped to meet leakage requirements Gas to trap: Formaldehyde, Acetoldehyde Impregnate: CamPure 8, Aluminium Impreg. KMn04 Relative Humidity: < 90% Temperature: 80°C maximum continues Controls: Individual test run for leakages (< 2,5 x 10-4) and pressure drop

Туре	Target contaminant	Dimensions WxHxD (mm)	Airflow/pressure drop (m³/h/Pa)	Weight (kg)	Optimum RH (%)
ActiCarb Nuclear	ICH3	305x610x292	600/300	43	≤90
ActiCarb Medical	lodine 131	610x610x292	1200/140	78	≤40
ActiCarb Medical	lodine 131	305x610x292	600/140	43	≤40
ActiCarb Nuclear	ICH3	610x610x292	1200/300	78	≤90
ActiCarb Mercury	Mercury	610x610x292	800/100	78	≤40
ActiCarb Mercury	Mercury	305x610x292	400/100	43	≤40
ActiCarb VOC	VOC	610x610x292	1800/300	71	≤50
ActiCarb VOC	VOC	305x610x292	900/300	43	≤50
ActiCarb Basic	Basic gas	610x610x292	1200/200	78	≤90
ActiCarb Basic	Basic gas	305x610x292	600/200	43	≤90
ActiCarb Acid	Acid gas	610x610x292	1200/200	78	≤90
ActiCarb Acid	Acid gas	305x610x292	600/200	43	≤90
ActiCarb ABEK	War gas	610x610x292	500/420	78	≤90
ActiCarb ABEK	War gas	305x610x292	250/420	43	≤90